

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 7006, UL Type SF-2 200°C, 600 V High Temperature Lead Wire**UL Type SF-2 200°C, 600 V High Temperature Lead Wire**

Silicon/Glass Braid
UL Listed
OSHA Acceptable

Stranded tinned Copper conductor, silicone rubber insulation, lacquered glass braid jacket (white), optional colors available on request

Application:

For use in wiring electronic and electrical equipment and appliances where a high temperature rating is required

SPECIFICATIONS

Conductor Size	18 AWG
Stranding	7/26 Tinned Copper
Insulation	Silicon Rubber
Insulation Thickness ¹	0.030 in
Jacket	Lacquered Glass-braid, White
Nom. Jacket Thickness	0.005 in
Nom. O.D.	0.123 in
UL Style	3071 SEW-1 SEW-2 SF-2
UL Rating	600 V, 200°C
UL Flame Test	VW-1
CSA Type	SEW-1
CSA Flame Test	FT-1

RoHS Compliant



RoHS Compliant

1 Treated with a high temperature lacquer finish