



Representative

**Catalog Number:** 1943  
**Product ID:** 7TAD013130R0000  
**UPC Number:** 78621001943  
**EAN Number:** 05414363138662  
**Status:** Active

3/4 Inch Chase Nipple, Malleable Iron, Nylon Insulated for Use with Rigid/IMC Conduit

### Header

3D Model Available on Website

### North American Specifications (UNSPSC)

UNSPSC	39131718 Electrical conduit nipple
IGCC	5753 Electrical conduit nipple
Brand Name	T&B
Type	Chase Conduit Nipple
Application	To Effectively Bush Factory or Field-Punched, Cut, or Drilled Holes In Metal Boxes or Enclosures. To Couple Boxes Back-to-Back
Standard	UL E23018, CSA
Material	Malleable Iron
Trade Size	3/4 Inch

### European Specifications (ETIM)

ETIM	EC001469 Protective hose adapter
Thread size outer thread metric	21
Material housing	Other
Material quality	Other
Surface protection	Untreated
Model	Straight

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	4.5x5x3
Outer Quantity	100
Outer Dimensions (inches)	9.4x6.9x5.8
Weight Uom	7 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-001846

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com