



Security Tech Germany

Aluminum 72 Series

Lightweight, Secure and Vibrant

ABUS lightweight aluminum 72 Series safety padlocks provide a simple and secure solution for lockout/tagout applications. This innovative, lightweight and vibrant padlock meets OSHA lockout regulations and is well suited for harsh industrial environments.



Key Features

- 6-pin cylinder offers maximum number of key differs and is available key-retaining or non-key-retaining
- Comes with 2 keys per lock, but can be ordered with 1 key per lock
- Lightweight, anodized aluminum body is perfect for laser engraving
- NANO PROTECT™-coated steel shackle offers extreme corrosion resistance; stainless steel shackle is also available
- Padlocks contain 78% recycled materials and are produced in a facility that achieved virtually zero waste to landfill operations in 2012 at a 98% diversion rate
- FDA-approved lubrication is ideal for use in the food industry
- Meets OSHA Lockout/Tagout Guidelines

Specifications



Product	Shackle Height	Body Width	#Pins in Cyl.	Key Options	Shackle Material
72/30	1 1/16"	1 3/16"	5	KA, KD, MK, GMK	NANO PROTECT™ Steel
72/40	1 1/16"	1 1/2"	6	KA, KD, MK, GMK	NANO PROTECT™ Steel
72/40HB40	1 9/16"	1 1/2"	6	KA, KD, MK, GMK	NANO PROTECT™ Steel
72/40HB75	3"	1 1/2"	6	KA, KD, MK, GMK	NANO PROTECT™ Steel
72/40HB100	4"	1 1/2"	6	KA, KD, MK, GMK	NANO PROTECT™ Steel

