



Security Tech Germany

Non-Conductive 74 Series

The Premier Safety Padlock

74 Series safety padlocks are designed for lockout/tagout applications and help keep equipment and employees safe from hazardous areas. This lightweight, non-magnetic, and dielectric padlock meets OSHA lockout regulations and is well suited for harsh industrial environments.



Key Features

- 6-pin cylinder offers maximum number of key differs and is key-retaining
- Comes with 1 key per lock
- Plastic-covered lock body and shackle are non-magnetic, and dielectric, providing intrinsically safe protection
- Under the plastic casing, the NANO PROTECT™-coated steel shackle and aluminum lock body are corrosion and chemical resistant
- Padlocks contain 70% recycled materials and are produced in a facility that achieved virtually zero waste to landfill operations in 2012 at a 98% diversion rate
- Ships with LOTO labels in English, Spanish and French
- Meets OSHA Lockout/Tagout Guidelines

Specifications



Product	Shackle Height	Body Width	#Pins in Cyl.	Key Options	Shackle Material
74/40	1 1/2"	1 1/2"	6	KA, KD, MK, GMK	NANO PROTECT™ Steel with Nylon Coating
74/40 KAx3	1 1/2"	1 1/2"	6	KA	NANO PROTECT™ Steel with Nylon Coating
74/40HB75	3"	1 1/2"	6	KA, KD, MK, GMK	NANO PROTECT™ Steel with Nylon Coating
74LB/40	1 1/2"	1 1/2"	6	KA, KD, MK, GMK	NANO PROTECT™ Steel with Nylon Coating