


## GFP25C15M -- Ground Fault Receptacles and Portable Unit



GFP6C15M  
GFP25C15M

Ideal for personal plug-in protection at marinas and onboard boats when used with pumps, drills, sanders and all portable electrical equipment. GFCI mechanism is watertight and approved for outdoor use. High visibility yellow SJTW-A power cord resists moisture, chemicals and sunlight.

Product Specifications	
<b>Product Type</b>	Ground Fault Receptacles and Portable Units
<b>GFCI Style</b>	Portable
<b>Portable GFCI Style</b>	Line Cord
<b>Rating</b>	15A 125V, 2p3w
<b>Length</b>	25'
<b>Blade Type</b>	Straight Blade
<b>Receptacle Type</b>	Standard
<b>Color</b>	 Yellow
<b>Poles and Wires</b>	2 Pole, 3 Wire Grounding
<b>Trip Level</b>	4-6 miliamps
<b>Trip Time</b>	.025 seconds nominal
<b>Frequency</b>	60 Hertz nominal
<b>Voltage</b>	120 volts +10%, -15%
<b>Max Interrupting Capacity</b>	2,000 amperes
<b>Max Humidity</b>	0.95
<b>Approvals</b>	UL
<b>UPC Number</b>	78358569039
<b>Weight in LBs</b>	3.4
<b>Link to Drawing Library</b>	<a href="#">Click here for Library</a>
<b>Link to PDF Catalog</b>	<a href="#">Click here for Catalog</a>

