

Kellems® Wire Management Products
Strain Relief Grips
Deluxe Cord Grips

HUBBELL

Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

Ordering Information

| Description | Form Size | UPC | Catalog Number |
|--|-----------|--------------|----------------|
| 90° Male Thread, Liquidtight, for Insulated Cables | F3 | 783585322629 | 07401081 |

Listings


UL Listed
CSA Certified

Specifications

| | |
|---------|-----------------|
| Strand | Stainless Steel |
| Body | Aluminum |
| Nut | Aluminum |
| Bushing | Neoprene |

Performance

| | |
|------------------------|---|
| Environmental | |
| Flammability | UL 94HB (Strand grip), UL 94V-2(Fitting) |
| Hazardous Locations | Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C |
| Operating Temperatures | -30°F to +240°F (-34°C to +115°C) |
| Wet Locations | Suitable for use in wet locations when used with a listed sealing ring between box and fitting |



Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

