

Heavy-Duty Computer Power Cord, 15A, 14AWG (NEMA 5-15P to IEC-320-C13), 6-ft.

MODEL NUMBER: P007-006



Highlights

- C13 to 5-15P Power Cable, 6 ft.
- 14 AWG x 3C - 15A - 125V
- RoHS Compliant
- UL Listed

Package Includes

- C13 to 5-15P Power Cable, 6 ft.

Description

Use Tripp Lite's P007-006 in server applications that require a higher rated, heavier gauge cable. C13 to 5-15P connectors, 3 x 14 AWG conductors, 15A / 125V rating.

Features

- Molded, Heavy-Duty Power Cable, 6 ft.
- IEC-60320-C13 to NEMA 5-15P
- 14 AWG x 3C, SJT, 15A, 125 Volt
- RoHS Compliant
- UL Listed

Specifications

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Side B - Connector 1	IEC-320-C13
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>