



SPECIFICATION SHEET

09-K1400



KEVLAR® GLOVES WITH SOLID NITRILE GRIP

- G-Tek® CR, 100% Kevlar®, solid nitrile, smooth grip, 10 gauge, medium weight, EN Cut Level 3
- Kevlar® yarn is designed to be cut resistant, will not melt, ignite, or conduct electricity
- Seamless knit construction protects hands without sacrificing comfort or dexterity
- Solid nitrile grip improves puncture resistance from sharp objects
- Color coded hems for easy size identification
- Dupont Kevlar® brand fiber provides high tensile strength relative to its weight - up to five times stronger than steel

APPLICATIONS

- Material handling and glass handling
- Fishing Industries
- General maintenance
- Woodworking
- Sanitation, waste handling and recycling

CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin extract using high speed. Tumble dry on low to medium heat setting. Can be dry cleaned. DO NOT BLEACH.

TECHNICAL DATA

MATERIAL	Kevlar® / nitrile				
COLOR	Shell: ■ Yellow / Coating: ■ Black				
CUFF STYLE	Elastic knit				
SIZES	XS - XL				
PACKAGING	1 pair per bag, 12 pairs per dozen, 6 dozen per case				
CASE	17.7" x 11.8" x 8.7" / 45cm x 30cm x 22cm				
CASE WEIGHT	XS	S	M	L	XL
	10.4 lbs 4.7 kg	10.9 lbs 5.0 kg	11.3 lbs 5.1 kg	12.4 lbs 5.6 kg	13.3 lbs 6.1 kg
COO	Korea				
HARM CODE	6116.10.6500				



DIMENSIONS (in/cm)

	XS	S	M	L	XL
A	8.9 / 22.5	9.3 / 23.5	9.7 / 24.5	10.0 / 25.5	10.4 / 26.5
B	3.4 / 8.5	3.5 / 9.0	3.7 / 9.5	3.9 / 10.0	4.1 / 10.5
H	■ Green	■ Blue	■ Brown	■ Grey	□ White

PERFORMANCE PROPERTIES

EN388: 2342	ASTM F1790: 927 grams (ANSI 2)					
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

BARCODES

ITEM	BAG	DOZEN	CASE
■ 09-K1400/XL	---	01616314011993	02616314011993
■ 09-K1400/L	---	01616314011986	02616314011986
■ 09-K1400/M	---	01616314011979	02616314011979
■ 09-K1400/S	---	01616314011962	02616314011962
■ 09-K1400/XS	---	01616314021633	02616314021633

