

10-KS14CL, 10-KS18CL Specification Sheet

KEVLAR® KNITTED SLEEVES

PRODUCT DESCRIPTION:

Kut-Gard Kevlar® sleeves, cotton inner layer, two-ply, seamless rib knit.

- Dupont Kevlar® brand fiber provides high tensile strength relative to its weight - up to five times stronger than steel.
- Kevlar® yarn is designed to be cut resistant; will not melt, ignite or conduct electricity.
- · Double-ply for added protection.

Applications:

Offers arm cut protection for applications that require large object handling, perfect for reach application protection. Ideal for glass operations, metal stamping, sheet metal, automotive, food applications, electrical and light heat applications.

TECHNICAL DATA:

Knit Shell: 100% Kevlar®, cotton inner

Color: Yellow

Available Sizes: 14", 18"

Packaging: 144 each per case

Case Dimensions (cm) - 46 x 30.5 x 23 / (in) - 18.1 x 12 x 9.1

Case Weight: (14) 8.0 lbs / 3.6 kg (18) 10.5 lbs / 4.7 kg

Country of Origin/Harmonization Code: USA/6117.80.9540

Shelf Life: 5 years in cool, dry conditions.

Laundering Instructions:

Machine wash in warm water with detergent. Rinse well and spin extract using high speed. Tumble dry on Low to Medium heat setting. Can be dry-cleaned.

CUT RESISTANCE PROPERTIES:

- 673 ± 10% GRAMS (Score is for single layer)
- Method ASTM F1790-05
- ANSI/ISEA 105-2000 Level 3 Cut Resistance


BARCODE #	DOZEN	CASE
10-KS14CL	01616314058324	02616314058323
10-KS18CL	01616314015151	02616314015151



DIMENSIONS:

Size Available	<u>14</u>	<u>18</u>
Over Length (cm) - A (in)	35.6 14	45.7 18
Sleeve Width (cm) - B	7.6	7.6
(in)	3.0	3.0

Binding Color = Yellow



This document is the property of PIP and the information contained herein is proprietary to PIP.