

RG59 Coax Cable with F-Type Connectors, 6-ft.

MODEL NUMBER: **A200-006**



Highlights

- Double Shielded RG59 Coax
- Gold Plated screw type F connectors
- Fully molded ends ensure long life use

Package Includes

RG59 Coax cable with F-Type Connectors - 6ft

Description

Tripp Lite's RG59 Coax F-Type cables are constructed of double-shielded, 23 gauge, 75ohm Coax cable, and are used in video applications such as Cable, Satellite, and any peripherals with Coax F type threaded connections. 24K Gold plated connectors and fully molded ends ensure long life reliability and crystal clear video .

Features

- Double Shielded (Foil and Braid) RG59B/U Cable
- 24K Gold Plated screw type F connectors
- Fully molded ends ensure long life use
- Use with Cable or Satellite Receivers, VCR, DVD, Coax enabled TV

Specifications

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	F-TYPE (MALE) THREADED COAX



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Side B - Connector 1	F-TYPE (MALE) THREADED COAX
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>