


Cat6 Gigabit Bulk Solid Plenum-Rated CMP Cable - Gray, 1000-ft., TAA

MODEL NUMBER: **N224-01K-GY**



Description

With Tripp Lite's Category 6 Plenum Rated Bulk cable, you can stay ahead of the game by using this high-speed cabling to distribute data, voice and video. This Plenum rated cable is designed for premise (in-wall) cabling applications in air ducts and drop ceilings. Constructed with high-quality copper wire, near-end crosstalk levels are kept to a minimum. This 1,000ft. spool of bulk solid plenum cable makes industrial runs a snap for the do-it-yourself cable guy. General Cat6 patch cables are available in a variety of colors and sizes.

Features

- Designed for premise (in-wall) cabling applications in air ducts and drop ceilings
- Premium cabling for category 6, category 5e and category 5 applications
- Color: Gray / Length: 1000-ft.
- 24 AWG 4-pair solid cable with Gray Plenum (CMP) jacket
- Deliver stable performance up to 550MHz/ 1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in PVC cable as well ([N222-01K-GY](#) and [N222-01K-BL](#))
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

INPUT	
Cable Length (ft.)	1000

Highlights

- Premium cabling for Category 6, Category 5e and Category 5 applications-rated for 350 MHz/1 Gbps communications
- Designed to meet Category 6 specifications: reduces cross-talk and return loss
- IEEE 802.3ab
- 1,000ft Box PLENUM (CMP) 4-pair Solid UTP
- Designed for premise (in-wall) cabling applications in air ducts and drop ceilings
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.

Package Includes

- 1000-ft. Cat6 Gigabit Bulk 4PR Solid Plenum CMP Cable



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.triplite.com

Cable Length (m)	304.8
PHYSICAL	
Color	Gray
CONNECTIONS	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
CERTIFICATIONS	
Approvals	EIA/TIA CAT6 TIA/EIA- 568-B-2.1, DRAFT 9 standards
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.triplite.com/products/product-certification-agencies>