

Cat6 RJ45 Modular Connector Plug with Load Bar, Solid/Stranded Conductor Round Cat6 Wire, 100-pack

MODEL NUMBER: **N230-100**



Highlights

- 100 Pack Cat6 RJ45 Plug with Load Bar
- 50 Micron Gold Contacts
- Staggered design reduces NEXT

Package Includes

100 each RJ45 Cat6 Plugs and Load-Bars

Description

Tripp Lite Cat6 RJ45 plugs can be used with Solid or Stranded conductor Cat6 wire. Included Load-Bars add to ease of termination and virtually foolproof results. Staggered Up-Down design for enhanced performance and reduction of Near End Cross-talk (NEXT). 50 micro-inch gold contacts for durability and longevity. Polycarbonate housing, UL94-V2.

Features

- Unshielded Cat6 RJ45 plug with Load-Bar for easy termination
- 50 micron Gold plating
- Use with Solid or Stranded conductor 4-pair Cat6 cable
- Staggered nose pattern reduces NEXT
- Works with most available RJ45 crimp tools (excluding AMP)

Specifications

PHYSICAL	
Color	White
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>