


48-Port 1U Rack-Mount Cat6/Cat5 High Density 110 Patch Panel, 568B, RJ45 Ethernet

MODEL NUMBER: N252-048-1U





Highlights

- Space saving CAT6 Rated 48-port 1U 110 type Patch panel
- Removable "upper-deck" for easy punch down termination
- Built-in wire management loom
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

 48port, 1U, Cat6 110 punch down patch panel

Description

Tripp Lite's 1U, 48port, Cat6 High Density Patch panel frees up valuable rack real estate by condensing a typical 2U 48 port patch panel into 1U of space. The unique design allows for easy punch down termination. Simply unscrew 4 slotted thumbscrews to remove the "upper deck" punch down array. Punch down the "lower deck" cables first, then replace the upper deck, and punch down upper array. Integrated wire loom keeps cabling tidy and easy to route. Heavy Duty 14GA cold rolled steel construction. 110 connectors are color coded for either 568A or 568B wiring.

Features

- Space saving CAT6 Rated 48-port 1U 110 type Patch panel
- Removable "upper-deck" for easy punch down termination
- Built-in wire management loom
- Color coded for 568A/568B wiring
- Heavy Duty 14ga cold rolled steel construction
- Mounts in standard 19" Racks or Cabinets

Specifications

OVERVIEW	
Cable Type	Cat6/6a
PHYSICAL	
Unit Dimensions (hwd / in.)	1.75" x 19" x 4"
Unit Dimensions (hwd / cm)	4.45 x 48.26 x 10.16
Unit Weight (Ibs.)	3.60



Unit Weight (kg)	1.63	
Color	Black	
CONNECTIONS		
Connector A	HARDWIRE	
Connector B	HARDWIRE	
Ports	48	
Other Ports	48 x 110 IDC Punch Down	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.