

Duplex Multimode 62.5/125 LSZH Fiber Optic Cable, 1000-ft. Bulk

MODEL NUMBER: N549-01K



Highlights

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen (LSZH) jacket
- Zip-Cord Style

Package Includes

Carton of 1,000ft Duplex 62.5/125 Multimode cable

Description

Tripp Lite N549-01K bulk 62.5/125 multimode fiber optic cable is ideal for long backbone runs, or for making your own Fiber patch cables. Individual fibers surrounded by Kevlar yarn for maximum tensile strength and protection. Low-Smoke, Zero Halogen (LSZH) jacket.

Features

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen jacket
- Zip-Cord Style
- Cable marked every meter
- Temp Range: -20C to +70C
- Suitable for Indoor Use
- 7lb Reel

Specifications

OVERVIEW	
Clad Diameter	125mu
Core Diameter	62.5mu
Number of Fibers	2
Shipping Weight	7lb



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Cable Length (ft.)	1000
Cable Length (m)	304.8
PHYSICAL	
Color	Orange
ENVIRONMENTAL	
Operating Temperature Range	-20C to +70C
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	62.5 BULK
Side B - Connector 1	62.5 BULK
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>