

## Standard Computer Power Extension Cord, 10A, 18AWG (IEC-320-C14 to Right Angle IEC-320-C13), 2-ft.

MODEL NUMBER: P004-002-13RA



### Highlights

- UL Listed
- C13 Right Angle - C14
- 18AWG (0.824mm), SJT, 10A, 100-250V

### Package Includes

- 2-ft. universal AC power extension PC style male (IEC-320-C14) to PC style female (IEC-320-C13) Right Angle

### Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This handy 2ft. cord can be used to extend the power cord on any PC or device with a C14 plug. Features an IEC-320-C14 to IEC-320-C13 Right Angle connection. UL listed.

### Features

- UL Listed
- 2-ft. power extension cord for your PC or device with a C14 plug
- Plug type: IEC-320-C14 (male), to IEC-320-C13 (female) Right Angle
- 18AWG (0.824mm), SJT, 10A, 100-250V

## Specifications

INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.6
PHYSICAL	
Color	Black
CONNECTIONS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13 - RIGHT ANGLE
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>