

Heavy-Duty Computer Power Cord, 15A, 14AWG (IEC-320-C13 to NEMA L6-20P), 6-ft.

MODEL NUMBER: **P011-006**



Highlights

- C13 to L6-20P Power Cable, 6ft.
- 14 AWG x 3C, 250V
- RoHS Compliant
- UL Listed

Package Includes

- C13 to L6-20P Power Cable, 6ft

Description

Use Tripp Lite's P011-006 in server applications that require a higher rated, heavier gauge cable. C13 to L6-20P connectors, 3 x 14 AWG conductors, 15A/250V rating.

Features

- Molded, Heavy-Duty Power Cable, 6 ft.
- IEC-60320-C13 to NEMA L6-20P
- 14 AWG x 3C, SJT, 15A, 250 Volt
- RoHS Compliant
- UL Listed

Specifications

PRODUCT OVERVIEW	
Product Overview	Heavy-Duty C13 to L6-20P Power Cable
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Side A - Connector 1	NEMA L6-20P
Side B - Connector 1	IEC-320-C13
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>