

## Heavy-Duty Power Cord, 15A,14AWG (NEMA 5-15P to IEC-320-C15), 4-ft.

MODEL NUMBER: P019-004



### Highlights

- 4-ft. heavy-duty power cord, 5-15P-to-C15
- 125V, 15A, 14AWG, SJT
- UL Listed

### Package Includes

- 4-ft. Heavy Duty 14AWG Power Cord, 5-15P - to - C15

### Description

Tripp Lite's 5-15P-to-C15 power cords allow connection from high voltage network hardware utilizing C16 inlets with 5-15R receptacles. Heavy-duty 14AWG wire supports voltages up to 125V. Molded ends ensure a lifetime of use.

### Features

- Heavy-duty power cord supports up to 125V
- 125V, 15A, 14AWG, SJT
- Flexible 14AWG wire for easy routing
- Use with Cisco, HP and other hardware that uses C16 inlets
- UL Listed

## Specifications

MODEL TEXT	
Key Benefit	Connect network hardware with C16 inlets such as Ethernet switches, to outlets with 5-15R receptacles.
INPUT	
Cable Length (ft.)	4
Cable Length (m)	1.2
PHYSICAL	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Color	Black
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C15
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>