

## Heavy-Duty Power Extension Cord, 20A, 12AWG (IEC-320-C19 to Right Angle IEC-320-C20), 2-ft.

MODEL NUMBER: P036-002-20RA



### Highlights

- Molded, Heavy-Duty Power Cord, 2 ft.
- IEC-60320-C19 to Right Angle IEC-60320-C20
- 12AWG (3.31mm<sup>2</sup>) x 3C, SJTW, 20A, 100-250V
- RoHS Compliant

### Package Includes

- C19 to C20 Right Angle Power Cord, 2 ft.

### Description

Use Tripp Lite's P036-002-20RA in server applications that require a higher rated, heavier gauge cable, as well as situations where right angle cable exit is required. C19 to C20 connectors, 3 x 12ga (3.31mm<sup>2</sup>) conductors, 20AMP rated, 250V - ideal for use with Blade Server Chassis.

### Features

- Molded, Heavy-Duty Power Cord, 2 ft.
- IEC-60320-C19 to Right Angle IEC-60320-C20
- 12AWG (3.31mm<sup>2</sup>) x 3C, SJTW, 20A, 250Volt
- RoHS Compliant

## Specifications

INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.6
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	IEC-320-C20 - RIGHT ANGLE



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Side B - Connector 1	IEC-320-C19
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>