

Heavy-Duty Power Extension Cord, 15A, 14AWG (IEC-320-C19 to IEC-320-C14), 6-ft.

MODEL NUMBER: P047-006



Highlights

- C19 to C14 Power Cable, 6 ft.
- 14 AWG x 3C, 15A, 100-250V
- RoHS Compliant

Package Includes

- C19 to C14 Power Cable, 6ft.

Description

Tripp Lite Heavy Duty C19 to C14, 6 ft. Power Cable. Constructed with 3 x 14 AWG copper conductors, fully molded ends, 100-250V / 15A rating.

Features

- Molded, Heavy-Duty Power Cable, 6 ft.
- IEC-60320-C19 to IEC-60320-C14
- 14 AWG x 3C, SJT, 15A, 100-250 Volt
- RoHS Compliant

Specifications

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C19



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>