

Keyspan Mini DisplayPort to Active VGA Adapter, Video Converter for Mac/PC, 1920x1200/1080p (M/F), 6-in.

MODEL NUMBER: P137-06N-VGA



Description

Tripp Lite's P137-06N-VGA Mini-DisplayPort to VGA Adapter allows you to connect a Mac or PC with a Mini-DisplayPort or Thunderbolt™ output to a VGA monitor.

Ideal for Thunderbolt™ /Mini DisplayPort equipped laptops, Chromebooks, MacBooks and Microsoft Surface. Mac 10.11, Windows 10 Compatible.

Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Fully-molded ends ensure long life enjoyment. It features a simple plug and play design with an integrated chip that converts the digital Mini-DisplayPort signal to analog VGA; no drivers or setup needed. Simply plug the adapter into your Mini-DisplayPort source and connect your VGA cable between it and your monitor.

Unlike passive adapters, Active adapters convert both Single-Mode and Dual Mode (DP++) DisplayPort output. It is ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals.

Features

- Connect a VGA monitor to a Mac or PC with a Mini Displayport output
- Compatible with the Thunderbolt port on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p

Highlights

- Connect a VGA monitor to a Mac or PC with a Mini Displayport output
- Compatible with the Thunderbolt port on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

System Requirements

- Mac or PC with a Mini Displayport port; Compatible with the Thunderbolt port on Mac computers
- Monitor with a VGA port
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P137-06N-VGA-V2

Package Includes

- Mini-DisplayPort to Active VGA Adapter



- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

Specifications

MODEL TEXT	
Key Benefit	Connect a VGA monitor to a Mac or PC with a Mini Displayport output
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.24
PHYSICAL	
Color	White
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
CERTIFICATIONS	
Certifications	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>