

Keyspan Mini DisplayPort to DisplayPort Cable Adapter, Video Converter, 2560x1600 (M/F)

MODEL NUMBER: **P139-06N-DP**



Description

Tripp Lite P139-06N-DP converts a Mini-Displayport video out port on a MAC, or other computer, to Displayport, allowing attachment of a Displayport monitor or HDTV with Displayport input. Plug the adapter into the computer, and then a standard Displayport cable from the adapter to the monitor.

Features

- Connect a Displayport enabled Monitor to a MAC Mini-Displayport video port
- Plug and Play - no drivers or setup needed
- Displayport 1.1a Compliant
- HDCP Compliant
- Supports resolutions up to 2560 x 1600 @ 60Hz

Specifications

INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.2
PHYSICAL	
Color	White
CONNECTIONS	

Highlights

- Converts Mini Displayport on a MAC to Displayport Female
- Connect Displayport enabled monitor to a MAC computer
- Supports resolutions up to 2560 x 1600 @ 60Hz

Package Includes

6-inch Mini Displayport Male to Displayport Female Adapter



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>