

SpikeCube Series 1-Outlet Personal Surge Protector, Direct Plug-In, 600 Joules, 2 Diagnostic LEDs

MODEL NUMBER: **SPIKECUBE**



Highlights

- 1 outlet / direct plug-in
- 600 joule rating
- Diagnostic LEDs
- \$5000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Package Includes

- SPIKECUBE Surge Suppressor
- Warranty and instruction information

Description

The SPIKECUBE Surge Suppressor from Tripp Lite is a direct plug-in suppressor providing protection on one AC outlet. Its small size makes it ideal for protecting laptop computers, projectors and other portable electronics. A green "Protected" and red "Grounded" LED illuminates to indicate that adequate surge suppression is available. The unit has 600 joules of surge energy absorption. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 1 outlet; direct plug-in
- Surge energy absorption: 600 joules; 6,500 amps
- Diagnostic LEDs indicate protection present (green) and ground present (red)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(1) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15



INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Right-Angle Plug	0
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED Details	Protected (green) & Grounded (red)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	600
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400, 500, 500
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	0
Cable (Coax) Protection	0
Network (Ethernet) Protection	0
PHYSICAL	
Shipping Dimensions (hwd / in.)	6.50 x 4.10 x 2.50
Shipping Dimensions (hwd / cm)	16.51 x 10.41 x 6.35
Shipping Weight (lbs.)	.150
Shipping Weight (kg)	0.07
Unit Dimensions (hwd / in.)	2.50 x 1.90 x 1.80
Unit Dimensions (hwd / cm)	6.35 x 4.83 x 4.57
Unit Weight (lbs.)	.100
Unit Weight (kg)	0.05



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Material of Construction	Plastic
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Form Factors Supported	Direct plug in suppressor supports wall-mounting directly into AC receptacle
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>