

SUPDMB710HW - UPS Accessory - Hardwire PDU Module

MODEL NUMBER: **SUPDMB710HW**



Description

The SUPDMB710HW hardwire input/output PDU module converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models [SU10000RT3U](#) and [SU8000RT3U](#)) to a totally hardwired solution. Easy quick-connect terminal block allows installation of hardwire distribution module in minutes. Can accept input voltages of 208 or 240 VAC single phase power. Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections.

Features

- Converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models [SU10000RT3U](#) and [SU8000RT3U](#)) to a totally hardwired solution
- Easy quick-connect terminal block allows installation of hardwire distribution module in minutes
- Can accept input voltages of 208 or 240 VAC single phase power
- Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections

Specifications

OVERVIEW	
Accessories Type	PDU Module
OUTPUT	
Frequency Compatibility	50 / 60 Hz

Highlights

- Converts compatible SmartOnline Hot-Swappable Modular UPS systems to hardwire input and output
- For use with [SU10000RT3U](#) and [SU8000RT3U](#) UPS Systems
- Easy quick-connect terminal block installation
- Manual bypass switch supports hot-swap UPS power module replacement

System Requirements

- Use with [SU10000RT3U](#) and [SU8000RT3U](#) SmartOnline Hot-Swappable Modular UPS Systems

Package Includes

- Hardwire PDU with Bypass Switch
- Mounting Hardware
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Output Receptacles	Hardwire
Output Nominal Voltage	208/240V
INPUT	
Nominal Input Voltage(s) Supported	208V AC; 240V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	208; 240
PHYSICAL	
Shipping Dimensions (hwd / in.)	10.75 x 9 x 8
Shipping Dimensions (hwd / cm)	27.3 x 22.9 x 20.3
Shipping Weight (lbs.)	5.8
Shipping Weight (kg)	2.6
Unit Dimensions (hwd / in.)	5.25 x 7.5 x 6.5
Unit Dimensions (hwd / cm)	13.3 x 19.1 x 16.5
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.1
Material of Construction	Steel
CERTIFICATIONS	
Certifications	Tested to UL1778 (USA), CSA (Canada), RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>