

## Power It! 6-Outlet Power Strip, 15-ft. Cord, 5-20P Plug, Metal Housing

MODEL NUMBER: TLM615NC20



### Description

Tripp Lite's Power It! TLM615NC20 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment requiring heavy-duty 20-amp service. Includes 6 NEMA 5-15/20R outlets, 15-foot AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged metal case to stand up to the most demanding environments, illuminated power switch with transparent cover to prevent accidental shutoff and 20A integrated circuit breaker to prevent dangerous overloads. INPUT/OUTPUT: Input: NEMA 5-20P/Output: 6 NEMA 5-15/20R ELECTRICAL: 120V AC, 50/60Hz, 20A FORMAT: 20A corded power distribution strip

### Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 6 NEMA 5-15/20R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- Transparent switch cover snaps tight to prevent accidental shutoff
- Convenient keyhole slots provide secure mounting options for a wide variety of surfaces and applications
- Heavy-duty 20A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 15-foot AC power cord
- Rugged metal case provides extra safety and durability
- UL certification

### Highlights

- 6 NEMA 5-15/20R outlets
- Illuminated on/off switch with cover
- Rated for 20-amp electrical service
- 15 ft. power cord with NEMA 5-20P plug
- Rugged metal case
- Keyhole mounting slots

### Package Includes

- TLM615NC20 power strip
- Warranty information
- Instruction manual



## Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15/20R
Output (Watts)	2400
Circuit Breaker (amps)	20
Overload Protection	20A circuit breaker
Outlet Orientation	Single row of 6
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Input Connection Type	NEMA 5-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.5
Input Cord Gauge Type	SJT 12AWG
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Switches	Illuminated on/off switch controls power to all outlets
Locking Switch Cover	Transparent switch cover snaps tight to prevent accidental shutoff
PHYSICAL	
Shipping Dimensions (hwd / in.)	15.5 x 6.5 x 2.25
Shipping Dimensions (hwd / cm)	39.4 x 16.5 x 5.7
Shipping Weight (lbs.)	3.8
Shipping Weight (kg)	1.7
Unit Dimensions (hwd / in.)	13.75 x 2.5 x 2
Unit Dimensions (hwd / cm)	35 x 6.35 x 5.1
Unit Weight (lbs.)	3.6
Unit Weight (kg)	1.6
Material of Construction	Metal case
Integrated Keyhole Mounting Tabs	Keyhole slots enable mounting to a variety of surfaces



Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	41.3mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole slots = 261.92mm; Distance between end tabs = 330.17mm
<b>CERTIFICATIONS</b>	
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>