

TouchMaster 6-Outlet Under-Monitor Surge Protector, 6-ft. Cord, 1440 Joules, Tel/Modem Protection

MODEL NUMBER: **TMC-6**



Description

Tripp Lite's TOUCHMASTER COMPACT surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TOUCHMASTER COMPACT offers 6 total outlets, 6 foot cord and LEDs to warn of power and wiring problems. Heavy grade AC suppression rated at 1440 joules shields equipment from surges and line noise. Attractive, slim design is perfect for use under desktop computer monitors or notebook computers. Individual switches offer power control over connected equipment. \$50,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Slim, compact design perfect for use under desktop monitors and notebook computers

SUPPRESSION: AC: 150V RMS Clamping/1440 joules/400V UL1449 3rd Edition

Features

- 6 outlets
- 6-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax equipment; 6-ft. telephone cord included
- Surge suppression rating: 1440 joules
- EMI/RFI noise filtering

Highlights

- 6 outlets / 6-ft. cord
- 1440 joule rating
- Tel/modem surge protection
- Individual switches
- \$50,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

Package Includes

- TOUCHMASTER COMPACT surge suppressor
- 6-ft. phone cord
- Instruction manual and warranty information



- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green), "grounded" (red) status and "power on" (green)
- Always-on outlet provides power for equipment you always need on, even when the "master" switch is off
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Allows for the computer to be controlled by the "master" switch and other outlets to be controlled either the "master" switch or corresponding switch on the front panel
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	84000
Right-Angle Plug	1
USER INTERFACE, ALERTS & CONTROLS	
Switches	Includes 5 front panel AC power switches. 4 switches control individual outlets and 1 serves as a main power switch that controls all but the one marked "unswitched" on the back panel
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.triplite.com

SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1440
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150V
UL1449 Let Through Rating	400V - UL Verified
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	1
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	0
Network (Ethernet) Protection	0
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.25 x 12.5 x 14
Shipping Dimensions (hwd / cm)	5.72 x 31.75 x 35.56
Shipping Weight (lbs.)	3.4
Shipping Weight (kg)	1.54
Unit Dimensions (hwd / in.)	1.75 x 11.5 x 12
Unit Dimensions (hwd / cm)	4.45 x 29.21 x 30.48
Unit Weight (lbs.)	2.8
Unit Weight (kg)	1.27
Material of Construction	Plastic
Housing Color	Black
Receptacle Color	Black
Color (AC Line Cord)	Black
Form Factors Supported	Supports under monitor placement as a power control center for an entire PC system with peripherals
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>