

4-Port USB 2.0 Hi-Speed Ultra-Mini Compact Hub with Power Adapter

MODEL NUMBER: **U222-004-R**



Description

The ultra small 4-port USB 2.0 hub is the most versatile and powerful hub on the market. This USB 2.0 hub allows you to connect up to four USB devices to a single USB port on a PC/Mac/laptop. Meets or Exceeds USB 2.0 Specifications for hi-speed data transmission rates up to 480Mbps. Perfect for both the desktop and mobile user. For the mobile user, this full featured hub with built-in cable is pocket size and an ideal solution for the user on the go. All four ports support USB Battery Charging (BC) specification v1.2, providing up to 1.5A for fast charging of mobile devices. Includes a 100-240V, 5V, 2A power adapter. This USB 2.0 device is backwards compatible so that it will function with both USB 2.0 devices as well as USB 1.1 peripherals. Comes in a clamshell retail package.

Features

- USB2.0 Hub - 4-Port
- Supports all data transfer rates up to 480Mbps
- Compact design with built-in cable (6-in.), perfect for travel
- Plug-and-play/hot-swappable allows you to add or remove a device at any time
- Diagnostic LEDs indicate power and port status
- Bus-powered or self-powered
- All four ports support USB Battery Charging (BC) specification v1.2, providing up to 1.5A for fast charging of mobile devices
- Includes External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- Compatible with all major operating systems

Highlights

- Link multiple USB devices to 1 computer with ultra-compact hub
- Meets or Exceeds USB 2.0 Specifications
- Includes External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- All four ports support USB Battery Charging (BC) specification v1.2, providing up to 1.5A for fast charging of mobile devices

Package Includes

- **U222-004-R** USB2.0 4-Port Ultra-Mini Hub
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)



Specifications

OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A
OUTPUT	
Charging Ports / Amps	(4) 1.2A
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.2
PHYSICAL	
Color	Black
CONNECTIONS	
Ports	4
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(4) USB A (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>