



SPECIFICATION SHEET

155-4-16

CLASS
4

NOVAX® RUBBER ELECTRICAL INSULATING GLOVES, CLASS 4, 16 INCH

- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection
- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone Free

APPLICATIONS

- Power generation
- Electrical contractors
- Hybrid automotive repair/service/manufacturing
- Industrial plant maintenance
- Utilities

TECHNICAL DATA

MATERIAL	Natural Rubber
COLOR	Black with Orange Liner
CUFF STYLE	Rolled
SIZES	9 - 12
PACKAGING	1 pair per bag/box, 6 pair per case
CASE	21.8" x 8.7" x 3.8" / 55.3cm x 22.1cm x 9.7cm
CASE WEIGHT	19.5 lbs / 8.8 kg
COO	Malaysia



MAX USE VOLTAGE

CLASS	AC V RMS	DC V
4	36,000	54,000

10 NOVAX™ by G.B. INDUSTRIES
ANSI / ASTM CLASS 4 MADE IN MALAYSIA D120 TYPE I
MAX USE VOLT 36000V AC

DIMENSIONS (in/cm)

	9	10	11	12
A	16 / 41	16 / 41	16 / 41	16 / 41
B	4.1 / 10.5	4.7 / 12	5.3 / 13.5	5.9 / 15

BARCODES

ITEM	BAG	DOZEN	CASE
155-4-16/9	616314063671	---	02616314063679
155-4-16/10	616314063688	---	02616314063686
155-4-16/11	616314063695	---	02616314063693
155-4-16/12	616314063701	---	02616314063709

