




## Basic Segment LCD Drawing

Part Number: FDS(50.7x33.0)XMR-15S-6WP



### Features:

1. Viewing Angle: 6:00 o'clock
2. Display Mode: Positive, Reflective, TN type
3. Driving Voltage: 5V, Static
4. Operating Temperature: -25°C to 75°C

### Interface Pin Connections

PIN #	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20		
SEGMENT	COM		B-C	NC	NC	NC	NC	4DP	3E	3D	3C	3DP	2E	2D	2C	2DP	1E	1D	1C	1B		
PIN #	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40		
SEGMENT	1A	1F	1G	2B	2A	2F	2G	COL	3B	3A	3F	3G	NC	NC	NC	NC	NC	NC	NC	LOBAT		COM

### Mechanical Data

ITEM	STANDARD	UNIT
MODULE DIMENSION	50.7 x 33.0 x 2.8	mm
VIEWING AREA	46.7 x 18.4	mm
SEGMENT SIZE	12.7 x 7.0	mm