




Basic Segment LCD Drawing

Part Number: FDS(50.8x30.48)XMR-15S-6WP



Features:

1. Viewing Angle: 6:00 o'clock
2. Display Mode: Positive, Reflective, TN type
3. Driving Voltage: 4.5V, Static
4. Operating Temperature: -20°C to 70°C

Interface Pin Connections

PIN #	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
SEGMENT	1E	1D	1C	COL1	2E	2D	2C	COL2	3E	3D	3C	P1	4E	4D	4C	P2	5E	5D	5C	5G
PIN #	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
SEGMENT	5B	5A	5F	4G	4B	4A	4F	3G	3B	3A	3F	2G	2B	2A	2F	1G	1B	1A	1F	COM

Mechanical Data

ITEM	STANDARD	UNIT
MODULE DIMENSION	50.8 x 30.48 x 2.8	mm
VIEWING AREA	45.72 x 17.78	mm