




Basic Segment LCD Drawing

Part Number: FDS(69x29.5)XMR-15S-12WP



Features:

1. Viewing Angle: 12:00 o'clock
2. Display Mode: Positive, Reflective, TN type
3. Driving Voltage: 3V, Static
4. Operating Temperature: -30°C to 85°C

Interface Pin Connections

PIN #	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
COM 1	/	/	1F	1A	2F	2A	3F	3A	4F	4A	5F	5A	6F	6A	COM1	/	/	/
COM 2	/	COM2	1G	1B	2G	2B	3G	3B	4G	4B	5G	5B	6G	6B	/	/	/	/
COM 3	/	/	1E	1C	2E	2C	3E	3C	4E	4C	5E	5C	6E	6C	/	COM3	/	/
COM 4	COM4	/	1D	P1	2D	P2	3D	P3	4D	P4	5D	/	6D	P6	/	/	P5	BAT

Mechanical Data

ITEM	STANDARD	UNIT
MODULE DIMENSION	69.0 x 29.5 x 2.5	mm
VIEWING AREA	65.0 x 23.0	mm
SEGMENT SIZE	6.5 x 15.0	mm