




## Basic Segment LCD Drawing

Part Number: FDS(133.4x80.9)XAP-15S-6WP



### Features:

1. Viewing Angle: 6:00 o'clock
2. Display Mode: Positive, Reflective, TN type
3. Driving Voltage: 3.0V, Static
4. Operating Temperature: -10°C to 60°C

### Interface Pin Connections

PIN #	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
COM	COM	1A	1F	1G	1E	1D	1C	1B	P1	2A	2F	2G	2E	2D	2C	2B	P2	3A	3F	3G
PIN #	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
COM	3E	3D	3C	3B	P3	4A	4F	4G	4E	4D	4C	4B	P4	5A	5F	5G	5E	5D	5C	5E
PIN #	41	42	43	44	45	46	47	48	49	50	51	52	53	54	55	56	57	58	59	60
COM	P5	6A	6F	6G	6E	6D	6C	6B	12C	12B	12A	12F	12G	12E	12D	P11	11C	11B	11A	11F
PIN #	61	62	63	64	65	66	67	68	69	70	71	72	73	74	75	76	77	78	79	80
COM	11G	11E	11D	P10	10C	10B	10A	10F	10G	10E	10D	P9	9C	9B	9A	9F	9G	9E	9D	P8
PIN #	81	82	83	84	85	86	87	88	89	90	91	92	93	94	95	96				
COM	8C	8B	8A	8F	8G	8E	8D	P7	7C	7B	7A	7F	7G	7E	7D	COM				



### Mechanical Data

ITEM	STANDARD	UNIT
MODULE DIMENSION	133.4 x 80.9 x 2.8	mm
VIEWING AREA	127.8 x 70.2	mm
SEGMENT SIZE	15.0 x 26.5	mm