

### RIMLESS (OTG)



#### DESCRIPTION

**Stylish visitor's spectacle that can be used alone, or as an Over-The-Glass for today's smaller personal eyewear**

- Polycarbonate unilens
- Over-the-glass design fits over most prescription eyewear
- Can also be worn by itself as a safety glass
- Molded nose bridge design to fit the vast majority of users
- Indirect vent temples to reduced fogging
- Also meets CSA Z94.3 requirements for Canada
- 6 Base curve lens



*Polycarbonate lenses block 99.99% of the sun's ultraviolet rays. This ultraviolet protection has already been incorporated within the lens material when the lenses are being produced.*

#### TECHNICAL DATA

LENS	
TYPE	One Piece
MATERIAL	Polycarbonate 99.99% UVA and UVB light absorption
THICKNESS	2.0mm
BASE CURVE	6
FRAME	
DESIGN	Rimless OTG
MATERIAL	Polycarbonate
SAFETY STANDARDS	
ANSI Z87.1+	Yes
CAN/CSA Z94.3	Yes
PACKAGING	
PACKAGING	12 pair per inner box, 144 pair per case
CASE SIZE	cm: 59.3 x 36 x 40.5 in: 23.3 x 14.2 x 15.9
CASE WEIGHT	6.2 kg / 13.7 lbs
SINGLE PAIR WEIGHT	28 g / 0.99 oz
COUNTRY OF ORIGIN	Malaysia

HELPS PROVIDE PROTECTION FROM PROJECTILES AND IMPACT IN GENERAL USE APPLICATIONS.

#### ITEM NUMBERS & BARCODES

ITEM #	FRAME COLOR	LENS COLOR & COATING	UPC BARCODES		
			EACH	BOX	CASE
250-37-0980	Clear	Clear, Uncoated	616314130465	01616314130464	02616314130463
250-37-0900	Clear	Clear, Anti-Scratch	616314130472	01616314130471	02616314130470