

SEMI-RIMLESS

MEETS ANSI
Z87.1+

DESCRIPTION

Wraparound temples with rubberized tips gently grip the wearer's head.

- Lightweight, semi-rimless design provides all day user comfort
- Sleek, sporty style with wraparound lens protection
- Bayonet temples with flexible rubber tips offer a comfortable, secure fit
- Soft rubber nose pads help keep the glasses in place
- Supplied with an adjustable neck cord
- 9 Base curve lens



Polycarbonate lenses block 99.99% of the sun's ultraviolet rays. This ultraviolet protection has already been incorporated within the lens material when the lenses are being produced.

TECHNICAL DATA

LENS	
TYPE	Dual
MATERIAL	Polycarbonate 99.99% UVA and UVB light absorption
THICKNESS	2.0mm
BASE CURVE	9
FRAME	
DESIGN	Semi-Rimless
MATERIAL	Polycarbonate/PVC
SAFETY STANDARDS	
ANSI Z87.1+	Yes
CAN/CSA Z94.3	No
PACKAGING	
PACKAGING	12 pair per inner box, 144 pair per case
CASE SIZE	cm: in:
CASE WEIGHT	13 lbs / 5.9 kg
SINGLE PAIR WEIGHT	0.9 oz. / 26 g
COUNTRY OF ORIGIN	Taiwan

HELPS PROVIDE PROTECTION FROM PROJECTILES AND
IMPACT IN GENERAL USE APPLICATIONS.

ITEM NUMBERS & BARCODES

ITEM #	FRAME COLOR	LENS COLOR & COATING	UPC BARCODES		
			EACH	BOX	CASE
250-AN-10110	Black	Clear, Anti-Scratch	616314123290	01616314123299	02616314123298
250-AN-10111	Black	Clear, Anti-Scratch/Anti-Fog	616314123306	01616314123305	02616314123304
250-AN-10112	Black	Gray, Anti-Scratch	616314123313	01616314123312	02616314123311
250-AN-10113	Black	Light Blue, Anti-Scratch	899558001443	01616314122223	02616314122222
250-AN-10114	Black	Indoor/ Outdoor, Anti-Scratch	616314123320	01616314123329	02616314123328
250-AN-10115	Black	Blue Mirror, Anti-Scratch	616314123337	01616314123336	02616314123335
250-AN-10116	Black	Red Mirror, Anti-Scratch	616314123344	01616314123343	02616314123342
250-AN-10117	Red	Gray, Anti-Scratch	616314123351	01616314123350	02616314123359
250-AN-10118	Black	IR Shade 3.0, Anti-Scratch	616314123368	01616314123367	02616314123366
250-AN-10119	Black	IR Shade 5.0, Anti-Scratch	616314123375	01616314123374	02616314123373
250-AN-10120	Black	Amber, Anti-Scratch	616314123382	01616314123381	02616314123380
250-AN-10121	Camouflage	Brown, Anti-Scratch	899558002143	01616314122230	02616314122239
250-AN-10122	Camouflage	Amber, Anti-Scratch	616314123399	01616314123398	02616314123397
250-AN-10123	Camouflage	Gray, Anti-Scratch	616314122255	01616314122254	02616314122253
250-AN-10124	Camouflage	Brown, Anti-Scratch/Anti-Fog	616314161902	01616314161901	02616314161900
250-AN-10125	Black	Silver Mirror, Anti-Scratch	616314124433	01616314124432	02616314124431
250-AN-10126	Black	Gray, Anti-Scratch/Anti-Fog	616314146633	01616314146632	02616314146631
250-AN-10127	Camouflage	Amber, Anti-Scratch/Anti-Fog	616314161919	01616314161918	02616314161917
250-AN-10128	Camouflage	Silver Mirror, Anti-Scratch	616314161926	01616314161925	02616314161924

PROTECTIVE INDUSTRIAL PRODUCTS, INC.

800-262-5755 // 518-861-0144 fax // sales@pipusa.com // www.pipusa.com



This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.