

PETG SAFETY VISOR

SPECIFICATION SHEET

PETG .040

DESCRIPTION

PETG .040 Visor

- Made with virgin resin, which leads to better uniformity of the viewing area
- Universal hole pattern will fit most headgear and hard hat adapters in the market
- Ships with masking on both sides to prevent scratching
- Meets ANSI Z87.1 Requirements

TECHNICAL DATA

VISOR	
DIMENSIONS	cm: 20.3 x 39.3 in: 8 x 15.5
MATERIAL	Polyethylene Terephthalate Glycol (PETG)
THICKNESS	.040 in
TINT	Clear or Medium Green
SAFETY STANDARDS	
ANSI Z87.1	Yes
PACKAGING	
PACKAGING	100 per case
CASE SIZE	cm: 40.6 x 21.5 x 12 in: 16 x 8.5 x 4.75
CASE WEIGHT	11.4 kg / 25.1 lbs
SINGLE WEIGHT	113.4 g / 4.0 oz
COUNTRY OF ORGIN	USA



Clear, crisp and distortion free visibility while meeting the requirement standards that help provide protection from projectiles and impact in general use applications.

PETG VISORS ARE SUITABLE FOR GENERAL GRINDING APPLICATIONS.

ITEM NUMBERS & BARCODES ITEM # MATERIAL TINT EACH BOX CASE 251-01-5211 PETG Clear 616314080944 - 02616314080942 251-01-5212 PETG Medium Green 616314115493 02616314115491



800-262-5755 // 518-861-0144 fax // sales@pipusa.com // www.pipusa.com

