

SPECIFICATION SHEET 33-425LY



G-TEK® HV HI-VIS SEAMLESS KNIT POLYESTER GLOVE WITH POLYURETHANE COATED SMOOTH GRIP

- 13 gauge, seamless knit polyester shell offers increased comfort, finger dexterity and breathability
- Polyurethane (PU) coatings offer great puncture and abrasion resistance while offering excellent tactile sensitivity
- Knit Wrist helps prevent dirt and debris from entering the glove
- Breathable back for comfort
- Hi-Vis coloring makes this product very easy to see
- CFIA Approved

APPLICATIONS

- Electronic and computer assembly
- Quality control
- Inspection
- · General assembly

CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104° F or 40°C. A mild non-ionic laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumble dry at temperature not exceeding 140° F or 60° C.

TECHNICAL DATA

MATERIAL	Polyester with polyurethane coating on palm and fingers					
COLOR	Hi Vis Yellow					
CUFF STYLE	Continuous Knit					
SIZES	XS - XXL					
PACKAGING	1 pair per bag, 12 pairs per dozen, 25 dozen per case					
CASE	24.4" x 11.1" x 18.1" / 62cm x 28cm x 46cm					
CASE	XS	S	M	L	XL	XXL
WEIGHT (S-XL)	17.6 lbs 8.0 kg	18.7 lbs 8.5 kg	19.8 lbs 9.0 kg	20.9 lbs 9.5 kg	22.0 lbs 10.0 kg	23.1 lbs 10.5 kg
C00	China					

PERFORMANCE PROPERTIES

EN388: 3131						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
33-425LY/XS		01616314092175	02616314092174
33-425LY/S		01616314092182	02616314092181
33-425LY/M		01616314092199	02616314092198
33-425LY/L		01616314092205	02616314092204
33-425LY/XL		01616314092212	02616314092211
33-425LY/XXL		01616314092229	02616314092228



DIMENSIONS (in/cm)

	XS	S	M		XL	XXL
A	7.5 / 19.0	8.5 / 21.5	8.9 / 22.5	9.3 / 23.5	9.6 / 24.5	10.0 / 25.5
В	3.2 / 8.2	3.3 / 8.4	3.4 / 8.7	3.7 / 9.5	3.9 / 9.9	4.1 / 10.3
Н	Purple	Red	Yellow	■ Brown	Black	■ Blue

