



SPECIFICATION SHEET

33-825



3121

G-TEK® MEDIUM WEIGHT SEAMLESS KNIT NYLON GLOVE WITH POLYURETHANE COATED SMOOTH GRIP

- 13 gauge, medium weight seamless knit nylon shell offers increased comfort, finger dexterity and breathability
- Polyurethane (PU) coatings offer great puncture and abrasion resistance while offering excellent tactile sensitivity
- Knit Wrist helps prevent dirt and debris from entering the glove
- Breathable back for comfort
- CFIA Approved

APPLICATIONS

- Electronic and computer assembly
- Quality control
- Inspection
- General assembly

CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104° F or 40°C. A mild non-ionic laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumble dry at temperature not exceeding 140° F or 60° C.

TECHNICAL DATA

MATERIAL	Polyester with polyurethane coating on palm and fingers					
COLOR	Shell: ■ Green, Coating: ■ Black					
CUFF STYLE	Continuous Knit					
SIZES	XS - XXL					
PACKAGING	1 pair per bag, 12 pairs per dozen, 25 dozen per case					
CASE	24.8" x 11.0" x 18.1" / 63cm x 28cm x 46cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	17.6 lbs 8.0 kg	18.7 lbs 8.5 kg	19.8 lbs 9.0 kg	20.9 lbs 9.5 kg	22.0 lbs 10.0 kg	23.1 lbs 10.5 kg
COO	China					

PERFORMANCE PROPERTIES

EN388: 3121	ANSI/ISEA Level 1 Cut Resistance					
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
■ 33-825/XS	---	01616314092052	02616314092051
■ 33-825/S	---	01616314092069	02616314092068
■ 33-825/M	---	01616314092076	02616314092075
■ 33-825/L	---	01616314092083	02616314092082
■ 33-825/XL	---	01616314092090	02616314092099
■ 33-825/XXL	---	01616314092106	02616314092105



DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	7.5 / 19.0	8.5 / 21.5	8.9 / 22.5	9.3 / 23.5	9.6 / 24.5	10.0 / 25.5
B	3.2 / 8.2	3.3 / 8.4	3.4 / 8.7	3.7 / 9.5	3.9 / 9.9	4.1 / 10.3
H	■ Purple	■ Red	■ Yellow	■ Brown	■ Black	■ Blue

