



SPECIFICATION SHEET

33-B125



G-TEK® KNIT NYLON GLOVE WITH POLYURETHANE COATED SMOOTH GRIP

- Seamless knit nylon shell offers increased comfort, finger dexterity and breathability
- Polyurethane (PU) coatings offer great puncture and abrasion resistance while offering excellent tactile sensitivity
- Knit Wrist helps prevent dirt and debris from entering the glove
- Breathable back for comfort
- CFIA Approved

APPLICATIONS

- Electronic and computer assembly
- Quality control
- Inspection
- General assembly

CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104° F or 40°C. A mild non-ionic laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumble dry at temperature not exceeding 140° F or 60° C.

TECHNICAL DATA

MATERIAL	Nylon with polyurethane coating on palm and fingers					
COLOR	■ Black					
CUFF STYLE	Continuous Knit					
SIZES	XS - XXL					
PACKAGING	1 pair per bag, 12 pairs per dozen, 25 dozen per case					
CASE	24.8" x 11.0" x 18.1" / 63cm x 28cm x 46cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	18.7 lbs 8.5 kg	19.8 lbs 9.0 kg	20.9 lbs 9.5 kg	22.0 lbs 10.0 kg	23.1 lbs 10.5 kg	24.3 lbs 11.0 kg
COO	China					

PERFORMANCE PROPERTIES

EN388: 4131	ANSI/ISEA Level 1 Cut Resistance					
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
■ 33-B125/XS	---	01616314054265	02616314054264
■ 33-B125/S	---	01616314054272	02616314054271
■ 33-B125/M	---	01616314054289	02616314054288
■ 33-B125/L	---	01616314054296	02616314054295
■ 33-B125/XL	---	01616314054302	02616314054301
■ 33-B125/XXL	---	01616314054319	02616314054318



DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	7.5 / 19.0	8.5 / 21.5	8.9 / 22.5	9.3 / 23.5	9.6 / 24.5	10.0 / 25.5
B	3.2 / 8.2	3.3 / 8.4	3.4 / 8.7	3.7 / 9.5	3.9 / 9.9	4.1 / 10.3
H	■ Purple	■ Red	■ Yellow	■ Brown	■ Black	■ Blue

