



# SPECIFICATION SHEET

## 34-500



### G-TEK® GP SEAMLESS KNIT NYLON GLOVE WITH NITRILE COATED MICROSURFACE GRIP - 13 GAUGE

- Nitrile "MicroSurface" coating provides a superior grip in dry, wet and oily conditions by reacting like tiny suction cups that attach themselves firmly to the material being handled
- Seamless knit nylon shell offers increased comfort, finger dexterity and breathability
- Knit wrist helps prevent dirt and debris from entering the glove
- Tremendous comfort and dexterity
- Strong protection from punctures and abrasions
- Seamless nylon liner for comfort and better fit
- Oil does not penetrate the glove like foam nitrile styles
- Open back for comfort

### APPLICATIONS

- General assembly of oily parts
- Metal handling,
- Fishing
- Machine operation.

### CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40° C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60° C)

### TECHNICAL DATA

MATERIAL	Nitrile, nylon
COLOR	Shell: ■ Blue / Coating: ■ Black
CUFF STYLE	Knitwrist
SIZES	XS - XXL
PACKAGING	1 pair per bag, 12 pairs per dozen, 12 dozen per case
CASE	22.4" x 13.8" x 9.8" / 57cm X 35cm X 25cm
CASE WEIGHT	19.0 lbs / 8.6 kg
COO	China

### PERFORMANCE PROPERTIES

EN388: 4121						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

### BARCODES

ITEM	BAG	DOZEN	CASE
■ 34-500/XS	---	01616314091994	02616314091993
■ 34-500/S	---	01616314092007	02616314092006
■ 34-500/M	---	01616314092014	02616314092013
■ 34-500/L	---	01616314092021	02616314092020
■ 34-500/XL	---	01616314092038	02616314092037
■ 34-500/XXL	---	01616314092045	02616314092044



### DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
<b>A</b>	9.1 / 23.0	9.4 / 24.0	9.8 / 25.0	10.2 / 26.0	10.8 / 27.5	11.2 / 28.5
<b>B</b>	3.1 / 8.0	3.5 / 9.0	3.7 / 9.5	3.7 / 9.5	3.9 / 10.0	4.19 / 10.5
<b>H</b>	■ Pink	■ Blue	■ Beige	■ Purple	■ Green	■ Grey

