



# SPECIFICATION SHEET

## 303-MVGZ4P



### ANSI CLASS 3 FOUR POCKET VALUE MESH VEST

- ANSI/ISEA 107 Class 2
- Breathable polyester mesh
- Zipper closure
- 2" silver reflective tape
- 2 lower internal pockets
- 2 external chest pockets, 1 including 4 pen pockets

### APPLICATIONS

- Construction
- Survey crews
- Utility workers
- Railway and metro workers
- Shipyards

### CARE INSTRUCTIONS

Recommend washing in tempered water not exceeding 104°F or 40°C. Wash in a 5-10 minute cycle time or hand wash. Rinse in cold water. Tumble dry at temperature not exceeding 104°F or 40°C, do not wring. Do not wash in biological powder, wash as synthetics. Maximum of 10 wash cycles.

### TECHNICAL DATA

MATERIAL	100% Polyester mesh
CONSTRUCTION	120g/m2 100% polyester 5*1 mesh fabric; silver reflective tape; #5 resin zipper
COLOR	<ul style="list-style-type: none"> <li><span style="color: yellow;">■</span> Hi-Vis Lime Yellow</li> <li><span style="color: orange;">■</span> Hi-Vis Orange</li> </ul>
SIZES	M - 5X
PACKAGING	1/Polybag, 50/Case
CASE	19.7" x 11" x 15.7" / 50cm x 28cm x 40cm
CASE WEIGHT	27 lbs / 12.2 kg
COO	China



### DIMENSIONS (in/cm)

	M	L	XL	2X	3X	4X	5X
<b>A</b>	47.2/120	49.6/126	52/132	54.3/138	56.7/144	59/150	61.4/156
<b>B</b>	28/71.1	28/71.1	28/71.1	28/71.1	28/71.1	28/71.1	28/71.1

### BARCODES

ITEM	BAG	DOZEN	CASE
303-MVGZ4P-LY/M	01616314079503	---	02616314079502
303-MVGZ4P-LY/L	01616314079510	---	02616314079519
303-MVGZ4P-LY/XL	01616314079527	---	02616314079526
303-MVGZ4P-LY/2X	01616314079534	---	02616314079533
303-MVGZ4P-LY/3X	01616314079541	---	02616314079540
303-MVGZ4P-LY/4X	01616314079558	---	02616314079557
303-MVGZ4P-LY/5X	01616314079565	---	02616314079564
303-MVGZ4P-OR/M	01616314079435	---	02616314079434
303-MVGZ4P-OR/L	01616314079442	---	02616314079441
303-MVGZ4P-OR/XL	01616314079459	---	02616314079458
303-MVGZ4P-OR/2X	01616314079466	---	02616314079465
303-MVGZ4P-OR/3X	01616314079473	---	02616314079472
303-MVGZ4P-OR/4X	01616314079480	---	02616314079489
303-MVGZ4P-OR/5X	01616314079497	---	02616314079496

