



# SPECIFICATION SHEET

## 280-AHS240

### MK8 EVOLUTION® FOR LINESMAN TYPE II HARD HAT

- Meets ANSI Z89.1-2014 Type II Class E requirements (Class C for Vented)
- Provides side, front & rear protection to the same level as ANSI Z89.1 Type I testing, with almost 20 times the coverage area
- Offers side (lateral) impact and penetration protection
- Expanded Polystyrene (EPS) Impact Liner helps absorb the forces of impact
- High-Density Polyethylene (HDPE) shell
- Mounted 4-point chin strap harness which is ANSI approved for retention on Type II helmets
- Deluxe polyester strap suspension with crown pad webbing
- Wheel ratchet size adjustment for true "one size fits all"
- Universal accessory slots
- Vented version is available to increase air circulation (280-AHS240V)

### APPLICATIONS

- Construction
- Oil & gas
- Mining
- Demolition
- High pressure jetting
- Energy companies
- Certain emergency services (FEMA & USAR)
- High-risk environments where high impact/side impact situations are of concern

### CARE INSTRUCTIONS

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

### TECHNICAL DATA

MATERIAL	Shell: High Density Polyethylene Liner: Expanded Polystyrene Suspension: Polyester / Polyethylene Sweatband: Microfiber Chin Strap: Polyester
COLOR	<input type="checkbox"/> White (-10) <input type="checkbox"/> Yellow (-20) <input type="checkbox"/> Blue (-50)
HAT SIZE	6 5/8 - 8 (20 7/8" - 25")
EACH WEIGHT	19.3 oz
PACKAGING	8 per case
CASE	11" x 9.75" x 20.75" / 27.9cm x 24.8cm x 52.7cm
CASE WEIGHT	13 lbs / 5.9 kg
COO	United Kingdom

### BARCODES

ITEM	EACH	DOZEN	CASE
<input type="checkbox"/> 280-AHS240-10	5038428120357	---	5038428810999
<input type="checkbox"/> 280-AHS240-20	5038428120364	---	5038428811002
<input type="checkbox"/> 280-AHS240-50	5038428120371	---	5038428811019
<input type="checkbox"/> 280-AHS240V-10	5038428158275	---	5038428813273



### DIMENSIONS (in)

	OSFA						
A	11.5						
B	6.375						

