

PETG .040

MEETS ANSI
Z87.1

DESCRIPTION

Clear PETG .040 Visor with Aluminum Binding

- Made with virgin resin, which leads to better uniformity of the viewing area
- Universal hole pattern will fit most headgear and hard hat adapters in the market
- Ships with masking on both sides to prevent scratching
- Meets ANSI Z87.1 Requirements

TECHNICAL DATA

VISOR	
DIMENSIONS	cm: 22.8 x 39.3 in: 9 x 15.5
MATERIAL	Polyethylene Terephthalate Glycol (PETG)
THICKNESS	.040 in
TINT	Clear
SAFETY STANDARDS	
ANSI Z87.1	Yes
PACKAGING	
PACKAGING	50 per case
CASE SIZE	cm: 45.7 x 33 x 13.3 in: 18 x 13 x 5.25
CASE WEIGHT	7 kg / 15.4 lbs
SINGLE WEIGHT	127.5 g / 4.5 oz
COUNTRY OF ORGIN	USA



Clear, crisp and distortion free visibility while meeting the requirement standards that help provide protection from projectiles and impact in general use applications.

PETG VISORS ARE SUITABLE FOR GENERAL GRINDING APPLICATIONS.

ITEM NUMBERS & BARCODES

ITEM #	MATERIAL	TINT	UPC BARCODES		
			EACH	BOX	CASE
251-01-7214	PETG	Clear	616314159435	---	02616314159433

PROTECTIVE INDUSTRIAL PRODUCTS, INC.

800-262-5755 // 518-861-0144 fax // sales@pipusa.com // www.pipusa.com



This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.