

## 64150NBU

NIGHT BREAKER UNLIMITED | Halogen headlight lamps for cars



### Areas of application

- Headlight

### Product benefits

- Up to 110 % more light on the road (compared to standard halogen lamps)
- Up to 40 m longer beam of light (compared to standard halogen lamps)
- Up to 20 % whiter light (compared to standard halogen lamps)
- Drivers spot obstacles and dangerous situations much sooner
- Optimum light for more reaction time
- Patented blue ring coating for less reflected glare
- More efficient light production thanks to optimized inert filling gas formula
- Higher resilience due to robust coil design

### Product features

- Eye-catching design with partial blue coating and silver cap

---

## Technical data

---

### Electrical data

Power input	68 W <sup>1)</sup>
Nominal wattage	55 W
Nominal voltage	12 V
Test voltage	13.2 V

<sup>1)</sup> Maximum

### Light technical data

Color temperature	3400 K
Luminous flux	1550 lm
Luminous flux tolerance	±15 %

### Dimensions & weight

Length	67.5 mm
Diameter	9.0 mm
Product weight	7.00 g

### Lifespan

Lifespan B3	150 h
Lifespan Tc	300 h

### Additional product data

Base (standard designation)	P14.5s
-----------------------------	--------

### Certificates & standards

ECE category	H1
--------------	----

### Country specific categorizations

Order reference	64150NBU
-----------------	----------

---

Disclaimer

---

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.