

# 64210NBU

### NIGHT BREAKER UNLIMITED | Halogen headlight lamps for cars



Areas of application

• Headlight

### **Product benefits**

- Up to 110 % more light on the road (compared to standard halogen lamps)
- Up to 40 m longer beam of light (compared to standard halogen lamps)
- Up to 20 % whiter light (compared to standard halogen lamps)
- Drivers spot obstacles and dangerous situations much sooner
- Optimum light for more reaction time
- Patented blue ring coating for less reflected glare
- · More efficient light production thanks to optimized inert filling gas formula
- Higher resilience due to robust coil design

#### **Product features**

• Eye-catching design with partial blue coating and silver cap



## Product datasheet

## Technical data

#### **Electrical data**

Power input	58 W <sup>1)</sup>
Nominal wattage	55 W
Nominal voltage	12 V
Test voltage	13.2 V

<sup>1)</sup> Maximum

#### Light technical data

Color temperature	3600 К
Luminous flux tolerance	±10 %

#### **Dimensions & weight**

Length	59.0 mm
Diameter	12.0 mm
Product weight	12.50 g

#### Lifespan

Lifespan B3	150 h
Lifespan Tc	250 h

#### Additional product data

Base (standard designation)	PX26d
-----------------------------	-------

#### Certificates & standards

	117
ECE category	H/

### Country specific categorizations

Order reference	64210NBU

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.