

ST 111 LONGLIFE

Starters for single operation at 230 V AC



Product features

- Temperature range for reliable cut-out: -20...+80 °C




Product datasheet

Technical data

Electrical data

Nominal voltage	220240 V
Nominal wattage	80.00 W
Mains frequency	5060 Hz

Dimensions & weight




Length	40.3 mm

Lifespan

Rated lamp life time	0 h
----------------------	-----

Additional product data

Lamp mercury content	0.0 mg	
Appropriate disposal acc. to WEEE	Yes	
Footnote only for product	Not suitable for L 70 W	



Circuit diagram

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4050300119588	ST 111 LONGLIFE	Shipping carton box 20	150 mm x 154 mm x 165 mm	3.81 dm ³	321.27 g
4050300270173	ST 111 LONGLIFE	Shipping carton box 1200	325 mm x 235 mm x 400 mm	30.55 dm ³	8086.00 g
4050300797878	ST 111 LONGLIFE	Shipping carton box 400	227 mm x 179 mm x 227 mm	9.22 dm³	2748.83 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.