
PUNCTOLED II

LED downlights



Product family datasheet

Technical data

Product description	Electrical data		Photometrical data				Light technical data	Dimensions & weight	
	Nominal wattage	Nominal voltage	Color temperature	Luminous flux	Light color as per EN 12464-1	Color rendering index Ra	Beam angle	Diameter	Height
PUNCTOLED II 10 W	10 W	220...240 V	3000 K	600 lm	Warm white	≥ 80	90 °	85.0 mm	54.0 mm
PUNCTOLED II 15 W	15 W	220...240 V	3000 K	1000 lm	Warm white	≥ 80	90 °	110.0 mm	73.0 mm
PUNCTOLED II 20 W	20 W	220...240 V	3000 K	1450 lm	Warm white	≥ 80	90 °	135.0 mm	76.0 mm

Product description	Colors & materials			Capabilities			
	Body material	Product color	Cover material	Type of installation	Adjustable	Dimmable	Type of connection
PUNCTOLED II 10 W	Aluminum	White	Aluminum	Recessed	No	Yes	Fixed (cutting terminal)
PUNCTOLED II 15 W	Aluminum	White	Aluminum	Recessed	No	Yes	Fixed (cutting terminal)
PUNCTOLED II 20 W	Aluminum	White	Aluminum	Recessed	No	Yes	Fixed (cutting terminal)

Product description	Certificates & standards		Country specific categorizations
	Protection class	Type of protection	Order reference
PUNCTOLED II 10 W	II	IP20	41079
PUNCTOLED II 15 W	II	IP20	41080
PUNCTOLED II 20 W	II	IP20	41081

Product family datasheet

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.