
LED RONDEL

Indoor LED ceiling luminaires



Areas of application

- Ideal as mirror lighting in bathrooms and cloakrooms
- Corridors
- Constant economical lighting in retail outlets, reception areas, offices and corridors

Product benefits

- Impressive for its low-profile design
- Pleasant homogenous light
- High-quality materials
- Creates a pleasant, calm atmosphere

Product features

- Surface-mounted luminaire with direct/indirect lighting
- Type of protection: IP44
- Coated steel casing
- Protection class: II (230 V AC)



Product family datasheet

Technical data

Product description	Electrical data				Photometrical data				Dimensions & weight
	Operating mode	Nominal wattage	Nominal voltage	Mains frequency	Color temperature	Luminous flux	Light color as per EN 12464-1	Color rendering index Ra	Diameter
LED RONDEL 20 W	ECG	20 W	220...240 V	50/60 Hz	3000 K	1000 lm	Warm white	80	298.0 mm
LED RONDEL 20 W SENSOR	ECG	20 W	220...240 V	50/60 Hz	3000 K	1000 lm	Warm white	80	298.0 mm

Product description	Height	Colors & materials			Temperatures	Lifespan	Additional product data	Capabilities
		Body material	Product color	Cover material	Ambient temperature range	Lifespan	Equipped with lamp	Type of installation
LED RONDEL 20 W	70.0 mm	Steel	White	Polykarbonát (PC), UV stabilizace	-20...+40 °C	30000 h	Yes	Surface-mounted
LED RONDEL 20 W SENSOR	70.0 mm	Steel	White	Polykarbonát (PC), UV stabilizace	-20...+40 °C	30000 h	Yes	Surface-mounted

Product description	Adjustable	Dimmable	Type of connection	Accessories	Certificates & standards		Country specific categorizations
					Protection class	Type of protection	Order reference
LED RONDEL 20 W	No	No	Terminal, 3-pole	Screw / Dovels / Washers	I	IP44	41097
LED RONDEL 20 W SENSOR	No	No	Terminal, 3-pole	Screw / Dovels / Washers	II	IP44	41098

Product family datasheet

Equipment / Accessories

- Driver included
 - Decorative ring made of anodized aluminum
-

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.