

---

## ITT 500 W 235 V-0170 R7S

HALOTHERM | Infrared halogen lamps, quartz clear



---

### Areas of application

- Plastics, paper and printing industries
- Drying paint and varnishes
- Coil coating
- Keeping food warm in restaurants

---

### Product benefits

- Short response time
- High efficiency
- Precise controllability
- Long lamp life



# Product datasheet

## Technical data


### Electrical data

Nominal wattage	500.00 W
Nominal voltage	235 V
Nominal current	2.1 A
Lamp current	2.10000 A
Construction voltage	235 V

### Photometrical data

Color temperature	2350 K
-------------------	--------

### Dimensions & weight



Diameter	10.0 mm
Length	250.7 mm
Filament length	170.00 mm

### Lifespan

Lifespan	5000 h
----------	--------

### Additional product data

Base (standard designation)	R7s
-----------------------------	-----

### Capabilities

Burning position	Any
Fuse, quick-acting	4.0 A

## Country specific information

Product code	METEL code	SEG-No.	STK number	UK Org
--------------	------------	---------	------------	--------

# Product datasheet

---

4008321203519	OSRHALOTT500	-	4739785	-
---------------	--------------	---	---------	---

---

## Product datasheet

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321203519	ITT 500 W 235 V-0170 R7S	Folding carton box 1	30 mm x 26 mm x 303 mm	0.24 dm <sup>3</sup>	37.67 g
4008321203526	ITT 500 W 235 V-0170 R7S	Shipping carton box 12	117 mm x 95 mm x 315 mm	3.50 dm <sup>3</sup>	485.75 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.