

# 6289-0356 Stainless Steel Footswitch 335325



- Versatile compact footswitch
- Durable and reliable with steel housing for long life and reliability
- Low profile to reduce operator fatigue
- Stainless steel (Grade 316) cover & base with black tread
- Single pole change over contacts
- Supplied with 2 metres of 4 core cable
- Sealed to IPX7
- 3A 250V AC
- Operating Temperature: -5°C to +40°C



## Outline Dimensions

