

## **ENGLISH**

Datasheet

RS Pro 0.5kW Oil Filled Radiator, Floor Mounted, Type G -British 3-pin RS Stock No: 712-6073



### **Product Details**

RS Pro 0.5 kW oil filled radiator has type G - British 3-pin plug for connection and is floor mountable. It has power switch with confirmation light, rear and front feet / supports and integral carry handle.

#### **Features and Benefits**

- Power switch with confirmation light
- Integral carry handle
- Variable thermostat
- 6 heating fins
- Rear and front feet/supports



# ENGLISH

## **Specifications:**

Control Type	Thermostat
Depth	165 mm
Dimensions	660 x 370 x 165 mm
Heat Type	Convection
Height	660 mm
Maximum Output Power	0.5 kW
Mounting	Floor Mounted
Plug Type	Type G - British 3-Pin
Power Settings	1
Width	370 mm