

ENGLISH

Datasheet

RS Pro 1.5kW Oil Filled Radiator, Floor Mounted, Type G -British 3-pin RS Stock No: 712-6061



Product Details

RS Pro 1.5 kW oil filled radiator has type G - British 3-pin plug for connection and is floor mountable. This oil filled radiator features efficient floor standing wheels for easy rolling movement.

Features and Benefits

- Efficient floor standing wheels
- Variable thermostatic control
- Floor mountable



ENGLISH

Specifications:

Control Type	Thermostat
Depth	165 mm
Dimensions	660 x 370 x 165 mm
Heat Type	Convection
Height	660 mm
Maximum Output Power	1.5 kW
Mounting	Floor Mounted
Plug Type	Type G - British 3-Pin
Power Settings	3
Width	370 mm